


Product Information

Mod.R&S 06 | Rev.4 | Update 01/2019 | Page 1



3D TECHNO™



Usage N.B. : preheat the lower plate of the press for 20 seconds

- Mirror cut the material
- Weed the exceeding material
- Place the material on the garment with its polyester carrier
- Heat apply at the conditions shown on the right
- After the first 3 second of application, remove the carrier warmHeat apply again for 20 seconds


The final aspect of the decoration may vary, depending on the target fabric used.

Washing Wait at least 24 hours from application before washing. Washing resistance up to 40°C, best inside-out. Do not use bleach or other aggressive chemical agents. Not suitable for dry cleaning Suitable for tumble dryer, synthetic cycle.


The product is REACH compliant

<u>↓</u> A

Average thickness 200 microns



Transfer settings
Manual press
3 seconds at 140°C (284°F)
then 20 seconds at 140°C
high pressure (4-5 bar)
Automatic press
3 seconds at 155°C (311°F),
then 20 seconds at 155°C
high pressure (4-5 bar)







N.B. All information here contained are based on our experience.
We always recommend to perform a test before starting standard production.
For best results we suggest to store the product away from sunlight at temperatures between 18°C and 26°C





The product meets the Italian and EU regulations relating to its proper use, and to the (EU) regulation n. 1907/2006/EU REACH (Registration, Evaluation, Authorization and Restriction of Chemical substance). This document can be subject to variations. Updated versions are available on our website www.siser.com For further information, please contact our Sales Office. Thank you



TECHNOPLOT CAD Vertriebs GmbH Dorfstr. 17 85737 Ismaning Tel. +49 (0)89 996535-0 Fax. +49 (0)89 996535-45 E-Mail: info@technoplot.com Web: https://www.technoplot.de